


Sales Link

Shallow Center DrawerPart Number 4850



The overall outside height of the new drawer is approximately 2 3/4", providing significantly improved knee clearance for technicians working at the statior. The drawer mounts to the worksurface support beams, the same as all Arlink drawers.

The inside clearance height is 2 $\frac{1}{2}$ ", the front to rear inside depth is approximately 20" and the inside width is approximately 18 $\frac{1}{2}$ "

The full width handle also doubles as an armrest when working inside the drawer and enables easy access by either hand without the need to hunt for the handle while working.

High quality Accuride full extension slides are used for smooth, stable drawer operation.

The redesigned and improved drawer is priced almost 40% lower than its predecessor!

The part number is unchanged and remains 4850.

We will update the photograph on the front of the Dental Technicians Workstation brochure with the next printing. For now, use the photography on this Sales Link to show customers the look of the new drawer





Arlink Worldwide

PO Box 215 Burlington On Canada L7R 3Y2 Tel: 905 332 8484 888 559 4441

Fax: 905 332 8277 Email: sales@arlink.com Website: www arlink.com

Siemens ESD Services

Remmerden 5 3911 TZ Rhenen The Netherlands Tel: int + 31 317 398 787

Fax: int + 31 317 398 780 Email: info.sesds@siemens.nl Website: www.sesds.nl

Adaptable Workstation Systems

Designed for a Changing World SL024 May 2002 US